



## DUOFLEX



CARRIER: Non-Adhesive Clear Polyester

### APPLIES ON

- ☑ Cotton
- ☑ Polyester
- ☑ Acrylic & Similar Fabrics

### CARE

- Always respect the garment's instructions
- Allow 24 hours after application before washing
- Iron the backside only

### WASH

- Max 100°F
- Preferably inside out
- Do NOT bleach
- Do NOT Tumble-dry
- Do NOT Dry-clean

### STORE

- Up to 1 year
- In a dry room (60-85°F)
- Away from sunlight
- In vertical position



## DUOFLEX



CARRIER: Non-Adhesive Clear Polyester

### APPLIES ON

- ☑ Cotton
- ☑ Polyester
- ☑ Acrylic & Similar Fabrics

### CARE

- Always respect the garment's instructions
- Allow 24 hours after application before washing
- Iron the backside only

### WASH

- Max 100°F
- Preferably inside out
- Do NOT bleach
- Do NOT Tumble-dry
- Do NOT Dry-clean

### STORE

- Up to 1 year
- In a dry room (60-85°F)
- Away from sunlight
- In vertical position

## APPLICATION

1. Cut the material in reverse with the recommended blade
2. Weed the excess material
3. Heat press on the garment at 325°F & Protect the polyester carrier with silicone paper 30 sec - low pressure
4. Peel the carrier off when cold

## APPLICATION

1. Cut the material in reverse with the recommended blade
2. Weed the excess material
3. Heat press on the garment at 325°F & Protect the polyester carrier with silicone paper 30 sec - low pressure
4. Peel the carrier off when cold

Vizuell AS

Sundvollen Næringspark, Åsaveien89B, 3531 Krokkleiva  
32 16 16 20 - post@vizuell.no - Vizuell.no

Vizuell AS

Sundvollen Næringspark, Åsaveien89B, 3531 Krokkleiva  
32 16 16 20 - post@vizuell.no - Vizuell.no